

19" Patch Panel 24 Port Cat.6 0.5 U black

Opis

This Patch Panel by Delock can be mounted in a 19" rack. At the LSA blocks you can install up to 24 network cables with a punch down tool. The small overall height makes a high port density possible.



Numer artykułu 43316

EAN: 4043619433162

Kraj pochodzenia: China

Opakowanie: White Box

Szczegóły techniczne

- Connectors:
 - external: 24 x RJ45 jack
 - internal: 24 x LSA block
- For mounting in 19" racks, 0.5 U
- Cable routing 180°
- Shielded
- Cat.6
- TIA-568A/B pinout
- Cable diameter up to 0.644 mm (22 - 24 AWG)
- For solid or stranded wire
- Metal housing
- Colour: jet black RAL 9005
- Dimensions (WxHxD): ca. 482.6 x 22.23 x 78.0 mm

Zawartość opakowania

- 19" Patch Panel
- Installation manual
- 24 x cable ties
- 4 x screws and caged nuts
- 48 x copper foil
- Insertion Tool und Cable Stripper Delock 18411



Ogólne

Jednostka wysokości:	0,5
Odpowiedni do średnicy przewodnika:	22 - 24 AWG
Typ montażu:	19 in

Interfejs

Zewnętrzne:	24 x RJ45 żeńskie
Wewnętrzne:	24 x blok zacisków LSA

Właściwości techniczne

Kategoria:	Cat.6
------------	-------

Właściwości fizyczne

Obudowa kolor:	czarny
Materiał obudowy:	metal
Tarcza:	shielded
Głębokość:	78 mm
Szerokość:	482,6 mm
Wysokość:	22.2 mm

Manufacturer information

Ulica	Beeskowdamm 13/15
Kod pocztowy	14167
Miasto	Berlin
Kraj	Deutschland
Email	info@delock.de
Strona internetowa	www.delock.de

