

In-Desk Hub 4 Port USB 5 Gbps

Description

This hub by Delock can be installed into an existing cut-out of the desk with a diameter of 60 mm or 80 mm to lead through the cables for the monitor, keyboard and mouse. At the same time, the hub offers four USB Type-A female ports. The data transfer and power supply is guaranteed through one USB 5 Gbps Type-A male and one USB 2.0 Type-A male. The distance between the free connectors can be maximum 20 cm, because the two cables are connected with each other.



Item no. 62868

EAN: 4043619628681

Country of origin: China

Package: Retail Box

Technical details

- Connectors:
top side:
4 x USB 5 Gbps Type-A female
bottom side:
1 x USB 5 Gbps Type-A male
1 x USB 2.0 Type-A male (power supply)
- Chipset: VL813
- Data transfer rate up to 5 Gbps
- Mounting diameter: 60 mm / 80 mm
- Mounting depth: 35 mm
- Cable length: ca. 95 cm
- Plug & Play

System requirements

- Linux Kernel 2.6 or above
- Mac OS 10.9 or above
- Windows 7/7-64/8.1/8.1-64/10/10-64/11
- PC or laptop with two free USB Type-A ports
- 60 mm or 80 mm cut-out of the desk

Package content

- In-Desk Hub
- 60 mm ring
- 80 mm ring
- User manual

Images



General

Function:	Plug & Play
Supported operating system:	Linux Kernel 2.6 or above Mac OS 10.12.1 Mac OS 10.9 or above Windows 10 32-Bit Windows 10 64-Bit Windows 7 32-Bit Windows 7 64-Bit Windows 8.1 32-Bit Windows 8.1 64-Bit

Interface

Top side:	4 x USB 5 Gbps Type-A female
Bottom side:	1 x USB 5 Gbps Type-A male 1 x USB 2.0 Type-A male (power supply)

Technical characteristics

Chipset:	VIA VL813
Data transfer rate:	5 Gbps

Physical characteristics

Cable length:	95 cm
Depth:	35 mm
Diameter:	80 mm 60 mm

Manufacturer information

Street	Beeskowdamm 13/15
Postal code	14167
City	Berlin
Country	Deutschland
E-Mail	info@delock.de
Website	www.delock.de

