

USB Type-C™ Adapter to HDMI 4K 60 Hz with USB Type-A and USB Type-C™ PD 95 W

Description

This adapter by Delock is suitable for the connection of a **HDMI monitor** to a computer with **USB-C™ interface** and DisplayPort alternate mode support. Thus, the adapter can be connected to different laptops like MacBook, Chromebook and similar. In addition, the adapter can also be operated on a Thunderbolt™ 3 or Thunderbolt™ 4 interface.

USB Power Delivery (USB PD 3.0) support up to 95 watt

This adapter has a **USB Type-C™ Power Delivery** port. If this port is connected to the power supply of the laptop or tablet, the host device is charged with up to 95 watts during operation.



Item no. 61063

EAN: 4043619610631

Country of origin: China

Package: Retail Box

Technical details

- Connectors:
 - 1 x USB Type-C™ male
 - 1 x HDMI female
 - 1 x USB 10 Gbps Type-A female
 - 1 x USB Type-C™ Power Delivery female
- DisplayPort 1.4 and High Speed HDMI with Ethernet (HEC) specification
- Resolution up to 3840 x 2160 @ 60 Hz (depending on the system and the connected hardware)
- Transmission of audio and video signals
- Output power for host: max. 95 W
- Supports 3D displays
- Supports HDR
- Supports HDCP 1.4 and 2.2
- Bootable
- USB bus powered
- Plug & Play
- Metal housing
- Cable length without connectors: ca. 15 cm
- Colour: grey

System requirements

- Android 13.0 or above
- Chrome OS
- Linux Kernel 6.2 or above
- Mac OS 13.1 or above
- Windows 10/10-64/11
- iPad Air (4th Generation) or above
- iPad Pro (3rd Generation) or above
- iPhone 15 Pro or above
- Surface Pro 7
- Device with a free USB Type-C™ port and DisplayPort alternate mode or with a free Thunderbolt™ 3 or Thunderbolt™ 4 port

Package content

- USB-C™ to HDMI Adapter + USB
- User manual

Images



General

Function:	Plug & Play
Supported operating system:	Chrome OS Surface Pro 7 Windows 10 32-Bit Windows 10 64-Bit iPad Pro (3rd Generation) or above iPad Air (4th Generation) or above Windows 11 Mac OS 13.1 or above Linux Kernel 6.2 or above Android 13.0 or above iPhone 15 Pro or above

Interface

Connector 1:	1 x USB Type-C™ male
Connector 2:	1 x HDMI female
Connector 3:	1 x USB 10 Gbps Type-A female
Connector 4:	1 x USB Type-C™ Power Delivery female

Technical characteristics

Maximum screen resolution:	3840 x 2160 @ 60 Hz
Signal transmission:	video audio

Physical characteristics

Housing material:	Aluminium
Cable length:	15 cm
Colour:	grey

Manufacturer information

Street	Beeskowdamm 13/15
Postal code	14167
City	Berlin

Country	Deutschland
E-Mail	info@delock.de
Website	www.delock.de