




MATERIAL:BRASS

THICKNESS:0.25

HARDNESS:SH

PLATING:TIN 40u' MIN

WIRE RANGE:(AWG)14-18

INSULATION O.D.:3.8 MAX.

VOLTAGE RATING:AC/250V,DC/350V

CURRENT RATING:AC,DC,10A

TEMPERATURE RANGE : -25°C TO +85°C

**DIMENSION:(MM)**

T:0.25 ± 0.03

L:20.5 ± 0.35

E:13.3 ± 0.25

W:3.6 ± 0.25

W1:4.5 ± 0.25

IS:5.0 ± 0.3

WS:3.3 ± 0.3

H:4.9 ± 0.3

H1:3.6 ± 0.3

D:3.2 ± 0.1

D1:2.0 ± 0.06


e:8.6 ± 0.3

RoHS  
Compliant

APPRO.  
核准 Helen

DWG.  
製圖 Yumi

DATE 制表日  
2011/01/26



SCALE  
比例 參考

UNIT  
單位 MM

PAGE  
張數 1 OF 1

TOLERANCE  
容許公差

0 ±  
.00 ±  
ANG. ±

SIZE  
紙張尺寸 A4

REV.  
版次 A

*Ninigi*

PART NAME 品名

JST 2.0mm FEMALE TERIMNAL BRASS  
MATERIAL TIN PLATING AWG14~18 ROHS

PART NO.

料號 TAMIYA-FT1