



2403E

Product no.: 2403E

Tip cutter - angled wide head. Wide, robust head, fine cut



The angled head provides for precise cuts at different working angles.



Similar to 503E, but with ergonomic handles



source images

The Perfect Cut - Strong, sharp and precise, every time

The Weller Erem Series 2400 Magic Sense is a range of medium-sized precision cutters that combines robustness, visibility and accessibility. A large variety of head shapes for precision work in hard-to-reach areas. The optimized ergonomic shape of the Series 2400 MagicSense prevents hand fatigue. These cutters are manufactured from improved induction-hardened cutting edges up to 64 – 65 HRC for an extremely long service life. The cutting edges are made from special tool steel. The precision cutters have a nonreflecting surface, are ESD safe and resharpenable.

Type		Type of Cut	Cutting Capacity	
Series 2400 MagicSense			mm	Inch
	2412E	 Semi Flush	0,5	0,019
	2422E	 Flush	1,0	0,039
	2432E	 Super Full Flush	0,8	0,031
	2477E	 Flush	1,0	0,039
	2403E	 Flush	1,0	0,039
	2404E	 Flush	0,8	0,031
	2482E	 Flush	0,6	0,023
	2475E	 Flush	0,4	0,015
	2470E	 Flush	0,4	0,015
	2476TX2	 Flush / Carbide	0,5	0,019



Swiss
Made



PRECISION TOOLS



Technical Data

Length mm	127
Length of cutting edges mm	9
Head width mm	11
Head thickness mm	6
Head length mm	20
Max. cutting capability – hard wire mm	---
Weight in oz	2.646
Length of cutting edges Inches	0.354
Head width Inches	0.433
Head thickness Inches	0.236
Head length Inches	0.787
ESD-safe	on
Cut	Flush
Max. cutting capability – medium hardness mm	Ø 1,0
Max. cutting capability – copper wire mm	Ø 1,6
Length inches	5
Weight in g	75
Erem applications	Microelectronic