



Data manager for communication between PC U Configuration via web browser, reading out via web browser, APP (SmartPhone, tablet), CSV. and Powermanager, data memory

Model		
product brand name	SETRON	
product designation	Multichannel current measuring device	
product type designation	7KT PAC1200	
General technical data		
measuring precision	Total accuracy +/-1% (of full-scale value / class 1)	
measured variable current rated value	63 A	
Supply voltage		
type of measurable line frequency full-scale value	50 +/- 5%	
line frequency rated value	Yes	
• 50 Hz		
Suitability		
suitability for use	Yes	
• ammeter		
• reactive power meter		
• revolution measuring instrument		
• frequency meter		
• pulse counter		
• voltmeter		
• wattmeter		
Mechanical Design		
height	85 mm	
depth	32.7 mm	
number of modular width units	4	
net weight	280 g	
Approvals Certificates		
General Product Approval	other	Environment

[Confirmation](#)



[Miscellaneous](#)

[Confirmation](#)

[Environmental Confirmations](#)

Environment

[Environmental Confirmations](#)

Further information

Information on the packaging

<https://support.industry.siemens.com/cs/ww/en/view/109813875>

Information- and Downloadcenter (Catalogs, Brochures,...)

<http://www.siemens.com/lowvoltage/catalogs>

Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=7KT1260>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/en/ps/7KT1260>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)

http://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=7KT1260

CAX-Online-Generator

<http://www.siemens.com/cax>

Tender specifications

<http://www.siemens.com/specifications>





