

1712E/1 - 2 - 3
Chwytyki magnetyczne, giętkie

F = zdolność podnoszenia

	art.	L mm	D mm	F kg	g
017120011	1712E/1	420	7,5	0,5	145
017120012	1712E/2	530	15	1,8	232
017120013	1712E/3	532	19	3,0	239

