SAK Series
Q 10 DLI

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Product image



Similar to illustration

Signal wiring
Tailored and particularly compact: with our AIO initiator/actuator terminal blocks, you are relying on an application-optimised solution for signal wiring. We also offer you other terminal blocks featuring spring and screw connection technology for signal wiring.

General ordering data

Type	Q 10 DLI
Order No.	1313100000
Version	SAK Series, Cross-connector, for cross-connection link, No. of poles: 10
GTIN (EAN)	4008190167622
Qty.	20 pc(s).

SAK Series
Q 10 DLI

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Technical data

Dimensions and weights

Width	59.9 mm	Width (inches)	2.358 inch
Height	4 mm	Height (inches)	0.157 inch
Depth	8 mm	Depth (inches)	0.315 inch
Net weight	6.895 g		

Material data

Material	CuSn	Colour	Grey

System specifications

Version	for cross-connection link	Tightening torque (cross-connector)	0.4...0.8 Nm
Mounting rail	none		

Additional technical data

Explosion-tested version	No	Installation advice	Direct mounting
Type of fixing	Screwed		

Dimensions

Pitch in mm (P)	6 mm

Rating data

Rated current	24 A

Classifications

ETIM 3.0	EC000489	ETIM 4.0	EC000489
ETIM 5.0	EC000489	ETIM 6.0	EC000489
UNSPSC	30-21-18-01	eClass 5.1	27-14-11-40
eClass 6.2	27-14-11-40	eClass 7.1	27-14-11-40
eClass 8.1	27-14-11-40	eClass 9.0	27-14-11-40
eClass 9.1	27-14-11-40		

Approvals

ROHS	Conform

Downloads

Brochure/Catalogue	CAT 1 TERM 16/17 EN
Engineering Data	EPLAN, WSCAD, Zuken E3.S
Engineering Data	STEP