



## BETA 666/C10X

Zero-Reset click-type torque wrench, in case, with sockets and extension bars



### Certifications and Standards



UNI EN ISO 6789

### Features

The 666/C10X enables reliable precision tightening while having everything you need for the task at hand and in order.

#### COMPLETE AND VERSATILE KIT

With its 15 pieces in the cassette, the kit includes everything needed for professional tightening operations.

#### ORDER AND DURABILITY

The impact- and wear-resistant materials of the bimaterial cassette prolong the life of the kit components, keeping them hemmed and secure inside.



#### REVERSIBLE RATCHETS

72-tooth mechanism for fast and precise use of the wrench, ensuring a recovery angle of only 5°.



#### DOUBLE GRADUATED SCALE

High scale visibility. Easily selectable setting with extremely precise increment.



#### BIMATERIAL HANDLE

The ergonomic handle provides a firm and secure grip. Made of materials resistant to fuels, oils and industrial liquids

## Certifications and Standards



UNI EN ISO 6789

666/10X: n. ZERO-RESET click-type torque wrenches □ 20÷100 Nm  
 920A: n. 1/2" square drive hexagon sockets □ 10÷22 mm  
 920/20 - 920/21: n. 1/2" drive extension bar 75-125 mm  
 920/15: n. 0 adaptor, 1/2" female and 3/8" male drives E 1/2 - B 3/8

## Coded items

|           | Art.     |
|-----------|----------|
| 006661011 | 666/C10X |

**Scan the QR Code to access the web tab**

Specs, media and documentation in one click.

