

USB Type-C™ Network Adapter 2.5 Gigabit LAN 1 x RJ45

Description

The adapter by Delock expands a PC or laptop by one network interface via the USB Type-C™ interface. In addition, the adapter can also be operated on a Thunderbolt™ 3 interface.

NBASE-T for higher speed

Modern services and new technologies require higher bandwidths. NBASE-T technology enables speeds of 1 Gbps and 2.5 Gbps with conventional networking cables. The best possible transmission rate is set automatically.



Item no. 65990

EAN: 4043619659906

Country of origin: China

Package: Retail Box

Technical details

- Connectors:
 - 1 x USB 5 Gbps USB Type-C™ male
 - 1 x 2.5 Gigabit LAN RJ45 jack
- Chipset: Realtek RTL8156
- SuperSpeed USB - 5 Gbps specification
- Data transfer rate:
 - Fast Ethernet up to 100 Mbps (Half/Full Duplex)
 - Gigabit Ethernet up to 1000 Mbps (Half/Full Duplex)
 - NBASE-T with up to 2.5 Gbps (Half/Full Duplex)
- Compatible with:
 - IEEE 802.3u: 100BASE-TX
 - IEEE 802.3ab: 1000BASE-T
 - IEEE 802.3bz: 2.5GBASE-T
- Supports Auto MDI-X (automatic detection of standard or crossover network cable)
- Supports IEEE 802.1Q Virtual LAN (VLAN)
- Supports IEEE 802.3az (Energy Efficient Ethernet)
- Support full duplex operation with IEEE 802.3x flow control and half duplex operation with back-pressure flow control
- Supports 9k Jumbo Frames
- LED indicator for power and activity
- USB bus powered
- Robust metal housing
- Colour: black

- Dimensions (LxWxH): ca. 67.0 x 39.2 x 21.3 mm
- Cable length without connectors: ca. 13.5 cm

System requirements

- Linux Kernel 3.2 or above
- Mac OS 10.7 or above
- Windows 7/7-64/8.1/8.1-64/10/10-64
- Device with a free USB Type-C™ port or with a free Thunderbolt™ 3 port

Package content

- USB Type-C™ 2.5 Gigabit LAN adapter
- User manual

Images



General

Specification:	USB 5 Gbps
Supported operating system:	Linux Kernel 3.2 or above Mac OS 10.7 or above Windows 10 32-Bit Windows 10 64-Bit Windows 7 32-Bit Windows 7 64-Bit Windows 8.1 32-Bit Windows 8.1 64-Bit
LED indicator:	power and activity

Interface

Connector 1:	1 x USB 5 Gbps USB Type-C™ male
Connector 2:	1 x Gigabit LAN RJ45 jack

Technical characteristics

Chipset:	Realtek RTL8156
Data transfer rate:	Fast Ethernet up to 100 Mbps Gigabit Ethernet up to 1 Gbps Gigabit Ethernet up to 2.5 Gbps

Physical characteristics

Housing material:	metal
Cable length:	13.5 cm
Length:	67.0 mm
Width:	39.2 mm
Height:	21.3 mm
Colour:	black

Manufacturer information

Street Beeskowdamm 13/15

Postal code	14167
City	Berlin
Country	Deutschland
E-Mail	info@delock.de
Website	www.delock.de