



## BETA 7356G

0-Gravity shoe, ultralightweight, made of water-repellent microfibre



### Certifications and Standards



S3L FO SR HRO

EN ISO 20345:2022

## Features

The 7356G features a water-repellent microfibre upper and offers a combination of comfort, style and safety.

### LIGHTNESS

The 0-Gravity shoe weighs approximately 100g less than the average work shoe. The approximate weight is 460g (measured on size 42)

### WATER PROTECTION

Made of water-repellent microfibre, the 0-Gravity 7356G offers a perfect balance of lightness, breathability and water resistance, representing a versatile and safe solution for those who never stop, even on the most demanding days

### COMFORT AND DURABILITY

The durable nitrile rubber outsole provides strength and stability, while the EVA outsole offers lightweight cushioning.

Ideal for those looking for a reliable and comfortable shoe.



### EVA FOAM UNDERFOOT COVER

The EVA underfoot cover, with a shock-absorbing heel pad, offers the perfect balance of support and comfort.



### SLIP-ON COLLAR

The elasticised slip-on collar is designed for easy donning.



### DESIGN AND STYLE

Safety does not go unnoticed, thanks to the upper details and innovative design.



## Certifications and Standards

CE S3L FO SR HRO EN ISO 20345:2022



## Specifications

LACING: traditional  
 WEIGHT (INDICATIVE SIZE 42): 460 g  
 TYPE: low

### Lightness

REMARKABLY LIGHTWEIGHT - approximate weight for size 42: 460 grams

### Comfort

EVA (Ethylene-Vinyl Acetate) FOAM underfoot cover with cushioning heel pad



### Safety

Toe cap: polymer material, 200 joules  
 Penetration-proof insole: composite fibre, ceramic treatment

### Protections

Tip: • Microfibre upper, water-repellent, with TPU (Thermoplastic Polyurethane) inserts  
 • Heel stability support  
 • Stretch slip-on collar  
 Durability: Sole:  
 • EVA (Ethylene-Vinyl Acetate) mid-sole  
 • Durable nitrile rubber tread

## Coded items

	Art.	EU	UK	 mm
073560038	7356G 38	38	5	254
073560039	7356G 39	39	6	261
073560040	7356G 40	40	6,5	268
073560041	7356G 41	41	7	274
073560042	7356G 42	42	8	281
073560043	7356G 43	43	9	288
073560044	7356G 44	44	10	294
073560045	7356G 45	45	10,5	301
073560046	7356G 46	46	11	308
073560047	7356G 47	47	12	314
073560048	7356G 48	48	13	321

Scan the QR Code to access the web tab

Specs, media and documentation in one click.

