

HT Hi Tech Polymers Oy

Inlet flange HTC-17 inlet flange

Code	HTC-17
Material	TPE-SEBS 50 Sha / TPE-SEBS 50 Sha V-0 / EMC
Colors	Grey RAL7035, V-0 white, EMC black
Measurements	C-hole: 216mm x 84mm Fastening hole 10mm Fasteningholes distance 193mm / 62mm
IP class	IP55
Temperature	-40C - +130C
Lead-throught	9 x 18mm-30mm / 10mm -14mm 4 x 10mm - 15mm 4 x 5mm - 10mm max 17 cabels
Other	Halogen-free, oil splatter resistant, in and outdoor
Electrical number	34 630 03 / 34 630 04
GTIN-code	6410034630038 / 6410034630045
Supplier	HT Hi Tech Polymers Oy
Packling size	100 pcs

