深圳格林威电子
GREENWAYCS

Tel:+0755-29756655
Fax:+0755-29756646

IP68 快速防水接线器/Quick waterproof connector

M684-D





ADD:Building 90,2nd Industrial area ,Lisonglang Community,Gongming Street,Guangming District, Shenzhen, China
中国·广东省·深圳市·光明区公明街道李松蔚社区第二工业区 90 栋
Website:www.greenwaycs.com

深圳格林威电子
GREENWAYCS
Tel:+0755-29756655
Fax:+0755-29756646

产品参数/Technical data

型号 Model	M684-D		
材料 Material	防火阻燃 Fire and flame retardant UL94V-2		
额定输出 Rated output	IEC/NSW:24A 450VAC ETL:10A 300VAC		
防护等级 IP code	IP68		
接线内芯 Terminal	2P/3P		
工作温度 Working	T105		
接线范围 Rated connecting capacity	欧规 European:0.5 ~ 2.5mm² 澳规 Australia:0.5 ~ 2.5mm² 美规 American:SJOW 14-18AWG		
密封胶塞/seal plug			
胶塞孔径/plug aperture	8mm	9mm	11mm
适用线径/Available cable diameter (橡胶圆线/Round rubber cable)	2*M20(4-8mm)	2*M20(5-10mm)	2*M20(6-11mm)
防水测试 Testing	20M 150hours		
参考剥线长度 Refer to stripping length	10mm（0.5~1.0mm²）rigid 15mm（1.5~2.5mm²）rigid		
产品尺寸 Product Size(参考实际尺寸图)	94.19*24.96mm（Refer to actual drawing）		
认证 Certification	ENEC,CE,UKCA,ETL,NSW,CB,ROHS		
产品质保/Product warranty	1 年/ one year		
产品应用/Application	水底/Underwater(淡水 fresh water) 地埋/Underground		


注/Mark:

1.不能使用在盐碱土壤/Do not use in saline soil
2.不能长期接触油性物质或浸泡在油污中/Do not contact oily substances or soak in oil for a long time
3.不建议长期在日照暴晒下使用/Long time explosed under sunshine is not recommended

ADD:Building 90,2nd Industrial area ,Lisonglang Community,Gongming Street,Guangming District, Shenzhen, China
中国·广东省·深圳市·光明区公明街道李松蔚社区第二工业区 90 栋
Website:www.greenwaycs.com


深圳格林威电子
GREENWAYCS
Tel:+0755-29756655
Fax:+0755-29756646

产品图纸/Product drawings



深圳市格林威电子有限公司	工程部（签名）	模具部（签名）	审 核（签名）	年、月、日（年月日）	料 号		产品图
	谢东						M684-D

参考剥线长度
Refer to stripping length



ADD:Building 90,2nd Industrial area ,Lisonglang Community,Gongming Street,Guangming District, Shenzhen, China
中国·广东省·深圳市·光明区公明街道李松蔚社区第二工业区 90 栋
Website:www.greenwaycs.com

深圳格林威电子
GREENWAYCS


Tel:+0755-29756655
Fax:+0755-29756646

接线步骤/Wiring steps

01

扭开两端螺帽套筒，取出接线内芯

Open the nut cover at both end sides,take out quick connector



02

将电缆穿过螺帽主体，扳起卡扣

Thread the cable through the nut body and pull up the buckle



03

两端电缆线相对应插入自锁接线内芯
将卡扣压合锁住线材即可

Connect the wires to the 3 core pressed terminal correspondantly press the levers



04

拧紧两端螺帽主体，接线完成

Twist and tighten the cable glands



ADD:Building 90,2nd Industrial area ,Lisonglang Community,Gongming Street,Guangming District, Shenzhen, China
中国·广东省·深圳市·光明区公明街道李松蔚社区第二工业区 90 栋
Website:www.greenwaycs.com