

# Mini USB 5 Gbps USB-C™ Memory Stick 32 GB - Metal Housing

## Description

This USB memory stick by Delock can be used to save and transport data, e.g. photos, videos or music. Thanks to the **USB Type-C™ connector**, the stick can be quickly and easily connected to various devices such as laptop, PC, smartphone, tablet or Smart TV.

### Small sturdy helper

Due to its small dimensions and its sturdy housing, this Delock USB stick is particularly suitable for travelling. Due to its **tiny size**, the USB stick fits into any trouser pocket.



**Item no. 54083**

EAN: 4043619540839

Country of origin: China

Package: Retail Box

## Technical details

- Connector: 1 x USB 5 Gbps USB Type-C™ male
- Capacity: 32 GB
- Maximum read speed: 140 MB/s
- Maximum write cycles: 3000
- Operating temperature: 0 °C ~ 70 °C
- Storage temperature: -25 °C ~ 85 °C
- Power consumption: max. 1.2 W
- Field of application: consumer
- Plug & Play
- Weight: ca. 5 g
- Dimensions (LxWxH): ca. 29.5 x 12.2 x 4.8 mm

## System requirements

- Android 9.0 or above
- Chrome OS 83.0 or above
- iPad Pro (2018)
- Linux Kernel 5.4 or above
- Mac OS 10.15.6 or above
- Surface Pro 7

- Windows 8.1/8.1-64/10/10-64/11
- PC or laptop with a free USB Type-C™ port
- PC or laptop with a free Thunderbolt™ 3 port

---

## Package content

- USB-C™ memory stick
- Key chain

---

## Images



## Interface

Connector:	1 x USB 5 Gbps USB Type-C™ male
------------	---------------------------------

## Technical characteristics

Storage temperature:	-25 °C ~ 85 °C
Operating temperature:	0° C - 70° C
Read:	140 MB/s
Maximum power consumption:	1.2 W
Maximum write cycles:	3000
Memory capacity:	32 GB

## Physical characteristics

Length:	29.5 mm
Width:	12.2 mm
Height:	4.8 mm

## Manufacturer information

---

Street	Beeskowdamm 13/15
Postal code	14167
City	Berlin
Country	Deutschland
E-Mail	info@delock.de
Website	www.delock.de