




Flexible strain relief for cables
model : F4.5x2.3/25-WH

Dimmension

Cable cross section (A)	4.5 x 2.3 mm
Total length (F)	23mm
Working length (E)	19mm
Width (B)	10.5mm
Width (D)	6.3mm
Mounting hole (C)	Max 6.5 x 2.7mm
Maximum mounting wall thickness (G)	3.9mm

Other

Material

Hydrogenated styrene butadiene block copolymer (SEBS)
Hydrogenated styrene isoprene butadiene block copolymer (SEEPS)
Ethylene Propylene Diene Monomer (EPDM)
Styrene butadiene styrene block copolymer (SBS)

