

USB-C™ KVM Switch to HDMI and DisplayPort 8K MST with USB 2.0

Description

This KVM switch by Delock is a convenient solution for connecting two computers with USB-C™ DP Alt Mode output to one HDMI and one DisplayPort monitor. Two monitors can be operated simultaneously at the outputs. By using the button you can switch between both computers.

Peripheral devices

Furthermore, three USB 2.0 ports for mouse and keyboard or USB storage can be connected.

USB powered

The device is powered via a USB port, a suitable USB cable is included. If no free USB-A port is available, an optional external power supply is required.

Multi-Stream Transport (MST)

The product is a Multi-Stream Transport (MST) hub and supports the extended desktop configuration of DisplayPort. In Windows, the connected monitors are controlled individually, and can be combined into one large display.



Item no. 11485

EAN: 4043619114856

Country of origin: China

Package: Retail Box

Technical details

- Connectors:
 - Input:
 - 2 x USB Type-C™ (DP Alt Mode) female
 - 1 x USB Type-C™ female (5 V power supply)
 - Output:
 - 1 x HDMI-A female
 - 1 x DisplayPort female
 - 3 x USB 2.0 Type-A female
- Switch button
- LED indicator for source
- Maximum resolution (depending on the system and the connected hardware):
 - 1 display: up to 7680 x 4320 @ 30 Hz
 - 2 displays: up to 3840 x 2160 @ 60 Hz
- Functions: Mirrored or Extended (Windows only)
- Metal housing

- Colour: anthracite
- Dimensions (LxWxH): ca. 115 x 54 x 12 mm

System requirements

- PC or laptop with a free USB Type-C™ port and DisplayPort alternate mode or
- PC or laptop with a free Thunderbolt™ 3 port
- Monitor or TV with HDMI connector
- HDMI cable
- Monitor or TV with DisplayPort connector
- DisplayPort cable
- Power source with a free USB Type-A female port

Package content

- KVM switch with USB
- 2 x Cable USB-C™ male to USB-C™ male, length ca. 80 cm
- Cable USB-C™ male to USB Type-A male, length ca. 100 cm (power supply)
- User manual

Images



Interface

Output:	3 x USB 2.0 Type-A female 1 x HDMI-A female
Input:	1 x USB Type-C™ female (power supply) 2 x USB Type-C™ female

Technical characteristics

Maximum screen resolution:	7680 x 4320 @ 60 Hz 3840 x 2160 @ 144 Hz
----------------------------	---

Physical characteristics

Housing colour:	anthracite
Housing material:	metal
Length:	115 mm
Width:	54 mm
Height:	12 mm

Manufacturer information

Street	Beeskowdamm 13/15
Postal code	14167
City	Berlin
Country	Deutschland
E-Mail	info@delock.de
Website	www.delock.de