





B - B

SPR750 LA53 X

Minimum centers:	1.91 (.075)
Full travel:	6.35 (.250)
Working travel:	4.30 (.169)
Current rating:	3 - 4 A
Probe resistance:	max. 10 mΩ
Plunger material:	Steel - Gold Plated
Barrel material:	Nickel Silver - Gold Plated
Spring material:	Music Wire - Gold Plated

Operating temperature: -40 °C up to +80 °C
(-40 °F up to +176 °F)

Spring force at working stroke: 2.80 N (10.1 oz)

© COPYRIGHT 2017
EQUIP-TEST KFT.
ALL RIGHTS RESERVED

	Name	Date
Designed	SMJ	2023.04.06.
Drawed		
Checked		

Catalog Item:
SPR750 LA53 X

This drawing, model, intellectual product belongs to Equip-Test Kft. Forwarding it to 3rd. party, copying it or using for any other purpose without the written approval of Equip-Test Kft., could entail to legal and criminal procedure!

Note

Drawing No.:

A3 SHEET 1 OF 1

EQUIPTEST
TEST ▪ SUPPORT ▪ INNOVATE