

Pushbutton, 15.2 mm, screw connector, momentary contact function, 1 NO, bezel black



Description

Pushbutton with mounting hole diameter 15.2 mm

Pushbutton with mounting hole diameter 15.2 mm, screw terminal



technical data

> general

Bezel color	black
Property of bezel / mushroom	opaque
Collar shape	round
Operating temperature, min.	-25 °C
Operating temperature, max.	85 °C
Storage temperature, min.	-40 °C
Storage temperature, max.	90 °C
illuminated	No
Packaging	Box
Packaging unit	100 pcs.
Net weight	5 g
Operating life	25,000 cycles
B10	32,500 cycles
Degree of protection, front side, according to DIN EN 60529	IP40 IP65 with sealing cap
Minimum order quantity (MOQ)	100 pcs.
RoHS compliant	Yes
REACH compliant	Yes
Country of origin	HU

direct links

> [RAFI eCatalog](#)

> mounting diameters

Outside dimension, width	19 mm
Mounting hole	15.2 mm
Mounting depth	21.5 mm
Installation height	8.2 mm

> mechanical data

Terminal on the rear	Screw terminal
Fixing	Threaded ring
Actuation function	momentary contact function
Operating force, max.	7.5 N
Operating travel, max.	3 mm
Contact function	1 NO

Contact system	Bridge contact
Contact material	Silver

> electrical data

Rated voltage, max.	250 V
Rated current, max.	0.7 A