



BETA 7273G FitEVOLUTION nubuck shoe, water-repellent



Certifications and Standards



S3S FO SR ESD

EN ISO 20345:2022

Features

The 7273G is the perfect synthesis of comfort and functionality: black outsole and details enhance the softness of the grey action nubuck upper.

FIT4YOU system

Create your own comfort with BETA's patented FIT4YOU system: a special cavity in the penetration proof insole allows you to replace the ETPU insole at any time, choosing from three different densities included in the pack.

ETPU inserts

ETPU is known for its excellent anti-shock and shock-absorbing properties. The three inserts soft, intermediate and rigid make it easy and immediate to customise the softness and support of the shoe to suit your needs.

Soft and resistant

The waterproof action nubuck upper is incredibly soft and comfortable, perfect for all-season use. It is also surprisingly durable, ideal for shoes built to last, without compromising on quality.

Metal-free

Composite toe cap and midsole are made of composite material to provide lightweight, metal-free protection.



FIT4YOU

The patented FIT4YOU technology, with the 3 ETPU inserts included in the pack, allows the shoe's cushioning to be personalised



Customised comfort

The special pressed sheet allows you to create your own comfort by choosing from 3 different ETPU inserts included in the pack.



ESD protection

ESD certified to protect user and machinery from electrostatic charges



Certifications and Standards

CE S3S FO SR ESD EN ISO 20345:2022



Specifications

LACING: traditional
WEIGHT (INDICATIVE SIZE 42): 590 g
TYPE: low

Lightness

- Water-repellent nubuck
- Heel stability support
- Traditional lacing

Comfort

Dual-density polyurethane

Safety

3-density cushioning ETPU insert and EVA FOAM underfoot cover

Protections

Tip: Polymer material, 200 joules.
Durability: Composite fibre, ceramic treatment.

Coded items

	Art.	EU	UK	 mm
072730137	7273G 37	37	4,5	251
072730138	7273G 38	38	5	257
072730139	7273G 39	39	6	263
072730141	7273G 41	41	7	276
072730140	7273G 40	40	6,5	269
072730142	7273G 42	42	8	282
072730143	7273G 43	43	9	290
072730144	7273G 44	44	10	296
072730145	7273G 45	45	10,5	304
072730146	7273G 46	46	11	311
072730147	7273G 47	47	12	317
072730148	7273G 48	48	13	324

