



Click [here](#) for the 3D model.

Dimensions

D	25mm MAX
T	25mm MAX
H	20.5mm MAX
LL	3.5mm +/-1mm
S	10mm NOM
S1	19mm NOM
Wire Size	0.9mm

Packaging Specifications

Packaging	Tray
Packaging Quantity	200
Typical Component Weight	19 g

General Information

Series	SC-JH
Style	Through-Hole
RoHS	Yes
Notes	Lead Spacing (S/S1) Are For Reference Only.
Miscellaneous	Temperature Rise Maximum: 55 K.
Core	Mn-Zn Ferrite

Specifications

Voltage AC	250 VAC
Inductance	2 mH (10 kHz)
Current	6 A
Temperature Range	-40/+120°C
DC Resistance	21.5 mOhms