


1256RTX**Końcówki wkrętakowe precyzyjne, profil Tamper Resistant Torx® 4 mm**

	art.	⊕	L mm
012560051	1256RTX 6	T6	27
012560052	1256RTX 7	T7	27
012560053	1256RTX 8	T8	27
012560054	1256RTX 9	T9	27
012560055	1256RTX 10	T10	27

