

Coaxial USB Type-C™ to DisplayPort cable (DP Alt Mode) 4K 60 Hz with braided coating 2 m

Description

This cable by Delock enables the connection of a DisplayPort monitor to a device with USB-C™ or Thunderbolt™ 3 port, such as a MacBook or a Chromebook. The interface has to support the DisplayPort Alternate Mode. The coaxial cable is very flexible and easy to handle due to its small diameter.



Item no. 81702

EAN: 4043619817023

Country of origin: China

Package: Zip poly bag

Technical details

- Connectors:
 - 1 x USB Type-C™ male
 - 1 x DisplayPort male
- Chipset: VIA VL103
- DisplayPort 1.2 specification
- Signal direction: USB Type-C™ input > DisplayPort output
- Cable gauge: 34 AWG
- Cable type: coaxial
- Cable diameter: ca. 3.8 mm
- With braided jacket
- Triple shielded cable
- Contacts gold-plated
- Transmission of audio and video signals
- Resolution up to 3840 x 2160 @ 60 Hz
(depending on the system and the connected hardware)
- Transmission of audio and video signals
- Supports 3D displays
- Supports HDCP 1.4
- USB bus powered
- Plug & Play
- Colour: black
- Length incl. connectors: ca. 2 m

Package content

- USB-C™ to DisplayPort cable

Images



General

Specification:	DisplayPort 1.2 HDCP 1.4
----------------	-----------------------------

Interface

Connector 1:	1 x USB Type-C™ male
Connector 2:	1 x DisplayPort male

Technical characteristics

Chipset:	VIA VL103
Maximum screen resolution:	3840 x 2160 @ 60 Hz

Physical characteristics

Cable category:	coaxial
Cable length incl. connectors:	2 m
Pin finishing:	gold-plated
Cable gauge:	34 AWG
Shielding:	triple
Colour:	black
Cable diameter:	3.8 mm

Manufacturer information

Street	Beeskowdamm 13/15
Postal code	14167
City	Berlin
Country	Deutschland
E-Mail	info@delock.de
Website	www.delock.de