

1164MQ
Szczypce płaskie odgięte 45° w izolacji do 1000V


	art.	L mm	L1 mm	 mm	A mm	B mm	C mm	D mm	 g
011640096	1164MQ160	160	54	1,6	19	3,0	5,0	9,0	140
011640100	1164MQ 200	200	76	1,6	20	3,5	5,5	10	200

