

3 Port In-Desk Hub USB 1 x USB Type-C™ and 2 x USB Type-A + HD-Audio Ports

Description

This hub by Delock can be installed into an existing cut-out of the desk with a **diameter of 60 mm** and can be connected to a computer via the USB Type-A interface. It expands the computer by **two USB Type-A ports** and **one USB Type-C™** port.

Cover cap and cable entry

The hub has a **cover cap** that protects the ports from dirt. In addition, a cable entry is available, whereby existing cables for e.g. mouse, keyboard and monitor can still be passed through the recess.



Item no. 62794

EAN: 4043619627943

Country of origin: China

Package: Retail Box

Technical details

- Connectors:
 - top side:
 - 1 x SuperSpeed USB (USB 3.2 Gen 1) USB Type-C™ female
 - 2 x SuperSpeed USB (USB 3.2 Gen 1) Type-A female
 - 1 x HD-Audio microphone 3.5 mm stereo jack female
 - 1 x HD-Audio speaker 3.5 mm stereo jack female
 - bottom side:
 - 1 x SuperSpeed USB (USB 3.2 Gen 1) Type-A male
- Chipset: VIA VL812
- Data transfer rate up to:
 - SuperSpeed USB 5 Gbps,
 - Hi-Speed 480 Mbps,
 - Full-Speed 12 Mbps,
 - Low-Speed 1.5 Mbps
- 1 x LED indicator
- Power supply: Bus-powered
- Mounting diameter: 60 mm
- Mounting depth: 43 mm
- Cable length: ca. 150 cm
- Plug & Play

System requirements

- Linux Kernel 3.3 or above
- Mac OS 10.15.3 or above
- Windows 8.1/8.1-64/10/10-64
- PC or laptop with a free USB Type-A port
- 60 mm cut-out in the desk

Package content

- In-Desk Hub
- Cover cap
- User manual

Images



General

Function:	Plug & Play
Mounting type:	in-desk
Supported operating system:	Linux Kernel 3.3 or above Mac OS 10.15.3 or above Windows 10 32-Bit Windows 10 64-Bit Windows 8.1 32-Bit Windows 8.1 64-Bit
LED indicator:	1 x

Interface

Connector 1:	1 x USB 5 Gbps USB Type-C™ female
Connector 2:	2 x USB 5 Gbps Type-A female
Connector 3:	1 x HD-Audio microphone 3.5 mm stereo jack female
Connector 4:	1 x HD-Audio speaker 3.5 mm stereo jack female
Connector 5:	1 x USB 5 Gbps Type-A male

Technical characteristics

Chipset:	VIA VL812
Data transfer rate:	5 Gbps
Voltage supply:	USB bus powered

Physical characteristics

Cable length:	1.5 m
---------------	-------

Manufacturer information

Street	Beeskowdamm 13/15
Postal code	14167
City	Berlin
Country	Deutschland
E-Mail	info@delock.de

Website

www.delock.de

