



Qoltec Power cable | SCHUKO CEE 7/7 angled plug | IEC C13 | 3x1.00mm | Pure copper Cu | 2.5m

Product code: 54622

Power cable designed for connecting electrical devices to a 230 V mains supply. Equipped with a standard IEC C13 connector and a SCHUKO plug (CEE 7/7), it ensures wide compatibility with popular office and home devices. The use of bare copper (BC) wires guarantees very good electrical conductivity, low energy losses and reliable operation of connected devices.


RELIABILITY AT HOME, IN THE OFFICE AND IN PROFESSIONAL ENVIRONMENTS



The power cable is designed for use at home and in the office

By choosing the **Qoltec Schuko/C13 cable**, you are getting a product that combines reliability with modern design and functionality. It is an excellent choice for anyone looking for proven solutions that will ensure **smooth operation and trouble-free performance of equipment, both in a home office and in demanding professional environments**. Trust the quality that guarantees complete satisfaction!

THE IDEAL SOLUTION FOR POWERING IT AND AUDIO-VISUAL EQUIPMENT




Schuko/C13 cable designed to power computers, monitors, printers and other office equipment

The Schuko/C13 power cable is the ideal solution for powering a wide range of devices with C14 sockets, such as:

- - desktop computers,
- - monitors,
- - printers,
- - televisions,
- - UPS emergency power supplies,
- - office equipment (fax machines, scanners).

Thanks to the **Schuko plug**, compatible with sockets throughout Europe, and the **IEC C13 connector**, which is standard in IT equipment, the cable offers the versatility and flexibility you need at home, in the office or in professional working environments.

HIGH QUALITY YOU CAN RELY ON EVERY DAY



H05VV-F power cable standard, PVC insulation, copper conductors

The exceptional quality of this **H05VV-F** standard cable guarantees durability and safety, even with intensive use. Solid **insulation made of polyvinyl chloride (PVC)** and **three high-quality copper multi-wire conductors** ensure stable power flow without the risk of overheating or failure. The appropriately selected **cable length of 2.5m** allows you to freely connect devices in hard-to-reach places, eliminating the problem of bulky, tangled cables.

TRUST BACKED BY A GUARANTEE



2-year product warranty

Do you care about the high quality of the product you buy? **Our solutions will meet your expectations.** Each of the power cables we offer is covered by a 24-month warranty valid from the date of purchase.

TECHNICAL DATA

Producer	Qoltec
Type	Power cable
Plug type	IEC C13/SCHUKO
Output current	16A 250V~
Standard of cable	HD5VV-F
Conductor cross-sectional area	3 * 1.00 mm
Insulating material	PVC
Application	All electrical appliances with the appropriate socket.
Usage	- Desktop computers - Monitors - Printers - Television - UPS emergency power supply - Office equipment (fax, scanner)
OTHER PARAMETERS	
Colour	Black
Working temperature	-20 C ~ +60 C
Cable length	2.5m
Package	Polybag
Package contents	1 x SCHUKO/C13 power cable
Package depth / length [mm]	390
Package width [mm]	105
Package height [mm]	30
Net weight [kg]	0.245
Gross weight [kg]	0.247
Warranty	24 month
EAN code	5901878546223