



Flexible strain relief for cables
model : R4.5/25

Dimmension

Cable cross section (A)

4.5mm

Total length (F)

25mm

Working length (E)

20mm

Width (B)

13mm

Width (D)

9.7mm

Mounting hole (C)

Max 6 x 6mm

Maximum mounting wall thickness (G)

3mm

Other

Material

Hydrogenated styrene butadiene block copolymer (SEBS)

Hydrogenated styrene isoprene butadiene block copolymer (SEEPS)

Ethylene Propylene Diene Monomer (EPDM)

Styrene butadiene styrene block copolymer (SBS)

