

Industry Hub 4 x USB 2.0 Type-A with 15 kV ESD protection and DIN rail mounting

Description

This **solid** industry capable USB Hub by Delock can be connected to a computer via the USB Type-A interface. It expands the computer by **four USB Type-A connectors**.

Screw connection and mounting option

Each USB port has two screw holes with M3 thread. Appropriate **cables can be plugged in and screwed** into the screw holes. This ensures a secure data connection even in mobile environments.

In addition, the hub comes with **wall mounting plates** and a **DIN rail bracket**, making it perfect for installation in an industrial environment.

ESD fuse

The USB ports are protected against electrostatic discharges up to **15 kV**.

Power supply

If necessary, an optional power supply or an optional power cable can be connected to the power socket. A voltage between 9 - 36 V can be applied to the terminal power connection, and 5 V to the DC connection.



Item no. 60686

EAN: 4043619606863

Country of origin: China

Package: Box

Technical details

- Connectors:
 - 1 x USB 2.0 Type-B female
 - 4 x USB 2.0 Type-A female
 - 1 x 5 V DC jack
 - 1 x 9 - 36 V 3 pin terminal power connector
- Chipset: Genesys Logic GL850G
- Data transfer rate up to 480 Mbps
- Bootable
- Plug & Play
- 1 x LED indicator
- Robust metal housing
- USB ports with screw holes
- Pitch of screw hole USB Type-A: ca. 19 mm
- Pitch of screw hole USB Type-B: ca. 19.5 mm

- Thread size: M3
- Removable wall-mount brackets
- Power supply: Bus-powered or Self-powered
- Flexible power supply with 9 V to 36 V at the terminal power connection
- ESD protection up to 15 kV for all ports
- Operating temperature: 0 °C ~ 60 °C
- Storage temperature: -10 °C ~ 70 °C
- Colour: black
- Dimensions (LxWxH): ca. 158 x 80 x 32 mm

Specification of power connector

- DC:
- 5 V
- Dimensions:
 - inside: ø ca. 2.1 mm
 - outside: ø ca. 5.5 mm
 - length: ca. 9 mm
 - terminal:
- 9 - 36 V

System requirements

- Linux Kernel 6.2 or above
- Mac OS 13.1 or above
- Windows 10/10-64/11
- Windows Server 2022
- PC or laptop with a free USB Type-A port

Package content

- Hub USB
- 1 x cable USB A male to USB B male, length ca. 1.8 m
- 2 x wall mounting brackets
- 1 x mounting for 35 mm DIN rail
- 1 x 3 pin terminal block
- User manual

Images



General

Function:	bootable
Supported operating system:	Windows 10 32-Bit Windows 10 64-Bit Windows 11 Windows Server 2022 Mac OS 13.1 or above Linux Kernel 6.2 or above
LED indicator:	1 x

Interface

Connector 1:	1 x USB 2.0 Type-B female
Connector 2:	4 x USB 2.0 Type-A female
Connector 3:	1 x 5 V DC jack
Connector 4:	1 x 9 - 36 V 3 pin terminal power connector

Technical characteristics

Chipset:	Genesys Logic GL850G
Data transfer rate:	480 Mbps
Storage temperature:	-10 °C ~ 70 °C
Operating temperature:	0 °C ~ 60 °C

Physical characteristics

Housing material:	metal
Length:	158 mm
Width:	80 mm
Height:	32 mm
Colour:	black

Manufacturer information

Street Beeskowdamm 13/15

Postal code	14167
City	Berlin
Country	Deutschland
E-Mail	info@delock.de
Website	www.delock.de

