

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0638197700](#)
Status: **Active**
Overview: [Application Tooling](#)
Description: Hand Crimp Tool for 3.96mm Pitch Wire-to-Wire and 6.50mm Pitch Wire-to-Board Crimp Terminals, 16-18 and 22 AWG

Documents:
[RoHS Certificate of Compliance \(PDF\)](#)

General
Product Family Application Tooling
Series [207129](#)
Comments Type: 4A
Function Crimp
Geographic Area Global
Level of Automation Manual
More Detailed Tech Information applicationtooling@molex.com
Overview Application Tooling
Product Name PremiumGrade
Tool Type Hand Crimp Tool
UPC 884982203693
Warranty Disclaimer CAUTION: Molex tooling crimp specifications are valid only when used with Molex terminals and tooling manufactured by Molex and sold by Molex or authorized distributors ("Molex Tooling"). When using tooling other than Molex Tooling with Molex specific connector systems listed in our ATS documents, the Molex tooling qualification does not apply and the responsibility for full qualification of the connector system is that of the customer. Molex accepts no liability for connector performance or tooling support where tooling other than Molex Tooling is used or where Molex Tooling is modified.

Physical
Net Weight 439.200/g

Material Info

Reference - Drawing Numbers
Application Tooling Documents
ATS-6381977HM, TM-638000029-001, TM-638000029CN-001, TM-638000029DE-001, TM-638000029FR-001, TM-638000029IT-001, TM-638000029JP-001, TM-638000029KR-001, TM-638000029MY-001, TM-638000029PL-001, TM-638000029RU-001, TM-638000029SK-001, TM-638000029SP-001, TM-638000029TH-001, TM-638000029TW-001, TM-638000029VN-001



Series image - Reference only

EU ELV
Not Relevant

EU RoHS **China RoHS**
Compliant
REACH SVHC
Not Contained Per -
ED/71/2019 (16 July 2019)
Halogen-Free
Status
Not Relevant

For more information, please visit [Contact US](#)

China ROHS	Not Relevant
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series
[207129](#) Series

Use With
[50597](#) , [50599](#) 3.96mm Pitch Wire-to-Wire and 6.50mm Pitch Wire-to-Board Crimp Terminals, 16-18 and 22 AWG

Application Tooling Description	FAQ Product #
CP-6.5 Wire-to-Board Crimp Terminal, Female, 16-22 AWG, Reel	505978000