

Pushbutton, 9.1 mm, 1 NO, momentary contact function, 1 NO, bezel black



Description

Pushbutton with mounting hole diameter 9.1 mm

Pushbutton with mounting hole diameter 9.1 mm, 1 NO

technical data

> general

Bezel color	black
Property of bezel / mushroom	opaque
Collar shape	round
Operating temperature, min.	-25 °C
Operating temperature, max.	70 °C
Storage temperature, min.	-40 °C
Storage temperature, max.	80 °C
illuminated	No
Soldering time for manual soldering, max.	3 sec
Soldering temperature for manual soldering	350 °C
Soldering	Manual soldering
Packaging	Box
Packaging unit	10 pcs.
Net weight	1.6 g
Operating life	40,000 cycles
B10	52,000 cycles
Degree of protection, front side, according to DIN EN 60529	IP40
Minimum order quantity (MOQ)	50 pcs.
RoHS compliant	Yes
REACH compliant	Yes
Country of origin	HU

> mounting diameters

Outside dimension, length	11 mm
Outside dimension, width	11 mm
Outside dimension, height	30 mm
Mounting hole	9.1 mm
Mounting depth	25.5 mm
Installation height	4.5 mm

direct links

> [RAFI eCatalog](#)

> mechanical data

Terminal on the rear	Solder terminal
Fixing	Threaded ring
Actuation function	momentary contact function
Operating force, max.	7 N
Operating force, min.	7 N
Operating travel, max.	2 mm
Contact function	1 NO
Contact system	Bridge contact
Contact material	Silver
Solderability	Yes

> electrical data

Rated voltage, max.	24 V
Rated current, max.	0.1 A