

USB 2.0 cable Type-A to Type-C 4 m

Description

This USB cable by Delock enables the connection between a device with a USB Type-C™ connector and a PC or a laptop equipped with a free USB port.



Item no. 83669

EAN: 4043619836697

Country of origin: China

Package: Zip poly bag

Technical details

- Connectors:
 - 1 x USB 2.0 Type-A male >
 - 1 x USB Type-C™ 2.0 male
- Cable gauge:
 - 26 AWG data line
 - 22 AWG power line
- Host = USB Type-A; Device = USB Type-C™
- Resistor: 56 kΩ
- Output current: up to 3 A
- Cable diameter: ca. 4.2 mm
- Data transfer rate up to 480 Mbps
- Colour: black
- Length incl. connectors (L): ca. 4.0 m

System requirements

- PC or laptop with a free USB Type-A port
- Device with USB Type-C™ port

Package content

- USB 2.0 cable

Images



General

Specification:	USB 2.0
----------------	---------

Interface

Connector 1:	1 x USB 2.0 Type-A male
Connector 2:	1 x USB 2.0 Type-CTM male

Technical characteristics

Data transfer rate:	480 Mbps
Maximum current:	3 A
Resistor:	56 kΩ

Physical characteristics

Pin finishing:	gold-plated
Cable gauge:	26 AWG data line 22 AWG power line
Shielding:	double
Length:	4 m
Colour:	black
Cable diameter:	4.2 mm

Manufacturer information

Street	Beeskowdamm 13/15
Postal code	14167
City	Berlin
Country	Deutschland
E-Mail	info@delock.de
Website	www.delock.de