

LED tape K-1490-24 14.9 W/m, IP20

Ref. K-1490-24



TECHNICAL SPECIFICATIONS

IP protection rating	20
CRI	90
LxBy	L80B50
Lifetime	61000 h
Input voltage	24 V DC
Power consumption	14.9 W/m
Beam angle	120°
MacAdam's ellipse	3 SDCM
Number of LEDs per 1 m	196
Number of LEDs per cut section	6 pcs
Warranty [months]	60

Color temperature	Lumen output	Efficiency	Ref
 2700 K	1100 lm/m	74 lm/W	K-27-1490-24
 3000 K	1175 lm/m	79 lm/W	K-30-1490-24
 4000 K	1250 lm/m	84 lm/W	K-40-1490-24