

PRODUCT-DETAILS

TY41M

CABLE TIE 65LB 10IN BK NYL PANEL MT



General Information

Extended Product Type	TY41M
Product ID	7TAG009520R0061
EAN	5414363064824
Catalog Description	CABLE TIE 65LB 10IN BK NYL PANEL MT
Long Description	Panel and Chassis Mounting Cable Tie, Black Polyamide (Nylon 6.6) for Temperatures up to 85 Degrees Celsius (185 F) for Indoor Applications, Length of 243.84mm (9.6 Inches), Width of 5.59mm (0.22 Inch), Thickness of 1.65mm (0.065 Inch), Tensile Strength Rating of 289 Newtons (65 Pounds), Mounting Hole Size of 8.13 - 17.27mm (0.32 - 0.68 Inch), Bulk Pack

Ordering

EAN	5414363064824
UPC	786210810942
Country of Origin	United States (US)
Customs Tariff Number	3926909985
Selling Unit of Measure	each

Dimensions

Product Net Width	0.22 in 5.59 mm
Product Net Depth / Length	9.6 in 243.84 mm

Container Information

Package Level 1 Units	500 piece
Package Level 2 Units	1000 piece
Package Level 2 Width	13.3 in 338 mm
Package Level 2 Height	13 in 330 mm
Package Level 2 Depth / Length	14.3 in 363 mm

Technical UL/CSA

Flammability According to UL94	V-2
--------------------------------	-----

Additional Information

Brand / Label	Ty-Rap
Bundle Diameter	2.37 in 60 mm
Color	Black
Effective Date	19821209
Lock Type	Stainless Steel Barb
Material	Nylon/Polyamide 6.6
Product Name	NYLON CABLE TIES AND ACCESSORIES
Product Type	Panel and Chassis Mounting
Tensile Strength	65 lb 289 N
Thickness	0.66 in 1.68 mm

Certificates and Declarations (Document Number)

Data Sheet, Technical Information	TY41M
Instructions and Manuals	TY41M

Classifications

ETIM 6	EC000046 - Cable tie
ETIM 7	EC000046 - Cable tie
ETIM 8	EC000046 - Cable tie
UNSPSC	39121703
WEEE Category	Product Not in WEEE Scope
IDEA Granular Category Code (IGCC)	5034 >> Cable ties

Categories

Low Voltage Products and Systems → Installation Products → Wire Management and Connectivity → Cable Ties

