


ASSMANN Y-power cord connection cable

AK-440403-017-S
EAN 4016032340430



Power Cord splitter cable, C14 - 2x C13 M/F, 1.7m, H05VV-F3G 1.0qmm/0.75qmm, bl

This Y-power cord used to connect the power supply unit of the PC with two monitor whereby one power socket less needs to be used. Additional you can use this cable for extension.

Approved for all European countries

- Connector 1: IEC C14, plug
- Connector 2: 2x C13, jack
- Cable standard: H05 VV F3G
- Current load capacity: 250V/10A

- Hoods: molded
- Shielding: Unshielded
- Lead cross-section: 1.0 / 0.75qmm
- Wire material: CU
- Connector surface: nickel-plated
- Color cable: black
- Color connector: black
- Length: 1.7 m
- Packaging: Polybag
- Assortment: Device Connection Cables

Logistische Daten						
	Anzahl (Stück)	Gewicht (kg)	Tiefe (cm)	Breite (cm)	Höhe (cm)	cm³
Karton-VPE	50	14,40	49,00	32,00	22,00	34.496,00
Innen-VPE	10	2,88	23,00	22,00	13,00	6.578,00
Einzel-VPE	1	0,29	3,00	18,00	18,00	972,00
Netto einzeln ohne VP	1	0,29	3,00	18,00	18,00	972,00