

Adapter USB Type-C™ male > HDMI female (DP Alt Mode) 4K 30 Hz + USB Type-A + USB Type-C™ PD

Description

This adapter by Delock is suitable for the connection of a HDMI monitor to a computer with USB-C™ interface and DisplayPort alternate mode support. Thus, the adapter can be connected to different laptops like MacBook, Chromebook and similar. In addition, the adapter can also be operated on a Thunderbolt™ 3 interface. Additionally the adapter has a USB 3.1 Type-A port and a USB-C™ port. The USB-C™ port can be used for power supply of the output device or to transfer data in USB 2.0 speed. Different USB devices such as docking stations, card reader, external enclosure etc. can be connected.



Item no. 62991

EAN: 4043619629916

Country of origin: China

Package: Retail Box

Technical details

- Connectors:
 - 1 x SuperSpeed USB (USB 3.1 Gen 1) USB Type-C™ male >
 - 1 x HDMI-A 19 pin female
 - 1 x SuperSpeed USB (USB 3.1 Gen 1) Type-A female
 - 1 x USB Type-C™ 2.0 Power Delivery female (optional for power supply)
- Chipset: VIA VL101 + VL813 + Parade PS176
- DisplayPort 1.2 and High Speed HDMI with Ethernet (HEC) specification
- Resolution up to 3840 x 2160 @ 30 Hz
(depending on the system and the connected hardware)
- Transmission of audio and video signals
- Supports 3D displays
- Supports HDCP 1.3
- USB bus powered
- Plug & Play
- Connectors: gold-plated
- 1 x ferrite core
- Metal housing
- Cable length without connectors: ca. 20 cm
- Colour: grey

System requirements

- Linux Kernel 4.3 or above
- Mac OS 10.12 or above
- Windows 7/7-64/8.1/8.1-64/10/10-64
- Windows 10 Mobile
- PC or laptop with a free USB Type-C™ port and DisplayPort alternate mode or
- PC or laptop with a free Thunderbolt™ 3 port

Package content

- USB-C™ to HDMI Adapter + USB Type-A

Images



General

Function:	Plug & Play
Specification:	DisplayPort 1.2 HDCP 1.3 HDMI 2.0
Supported operating system:	Linux Kernel 4.3 or above Linux Kernel 4.9 or above Mac OS 10.12 or above Windows 10 32-Bit Windows 10 64-Bit Windows 10 Mobile Windows 7 32-Bit Windows 7 64-Bit Windows 8.1 32-Bit Windows 8.1 64-Bit

Interface

Output:	1 x USB 5 Gbps Type-A female 1 x HDMI-A female
Input:	1 x USB Type-C™ female (power supply) 1 x USB Type-C™ male

Technical characteristics

Maximum screen resolution:	3840 x 2160 @ 30 Hz
Signal transmission:	video audio

Physical characteristics

Ferrite core:	1 x
Housing material:	Aluminium
Cable length:	20 cm

Manufacturer information

Street Beeskowdamm 13/15

Postal code	14167
City	Berlin
Country	Deutschland
E-Mail	info@delock.de
Website	www.delock.de