

1266BP
Wkrętaki z końcówką trzpieniową sześciokątną kulistą


	art.	mm	L mm	L1 mm	Ø mm	g
012660020	1266BP 2	2	100	200	2,5	34,6
012660025	1266BP 2,5	2,5	100	200	3	36,6
012660030	1266BP 3	3	125	225	3,5	41,6
012660040	1266BP 4	4	125	233	5	73,3
012660050	1266BP 5	5	120	239	6	105,3
012660060	1266BP 6	6	140	259	7	124,0
012660080	1266BP 8	8	160	287	9,5	202,0
012660100	1266BP 10	10	160	287	12	270,0

