



BETA 7201BP BASIC PLUS suede sandal with strap closure



Certifications and Standards



S1PS FO SR

EN ISO 20345:2022

Features

The metal-free 7201B suede sandals guarantee durability and maximum breathability with excellent value for money.

FIRST PRICE METAL FREE

The 7201BP sandal provides protection without metal parts, offering greater comfort and versatility of use, at a competitive price.

WIDE FOOTBED

The wide fit further enhances the comfort of the shoe, preventing possible constriction of the foot at any time of day.

NEW STANDARD EN ISO 20345:2022+A1:2024

The shoe is S1P S FO SR certified according to the latest EN ISO 20345:2022+A1:2024 standard. It is ideal for even the most demanding work environments, thanks to improved slip, oil and penetration resistance.



BREATHABLE

Perforated upper and mesh inserts promote foot ventilation, improving breathability



STRAP CLOSURE

The hook-and-loop fastener provides a secure and adjustable fit, offering ease of donning and a comfortable fit throughout the day.



Certifications and Standards

CE S1PS FO SR EN ISO 20345:2022



Specifications

LACING: tear-off
 WEIGHT (INDICATIVE SIZE 42): 570 g
 TYPE: low

Lightness

Suede with mesh inserts

Comfort

Dual-density polyurethane



Safety

Polyurethane foam

Protections

Tip: Polymer material, 200 joules
 Durability: Composite fibre, ceramic treatment

Coded items

	Art.	EU	UK	 mm
072010635	7201BP 35	35	2,5	229
072010636	7201BP 36	36	3,5	236
072010637	7201BP 37	37	4,5	243
072010638	7201BP 38	38	5	250
072010639	7201BP 39	39	6	257
072010640	7201BP 40	40	6,5	264
072010641	7201BP 41	41	7	271
072010642	7201BP 42	42	8	278
072010643	7201BP 43	43	9	285
072010644	7201BP 44	44	10	292
072010645	7201BP 45	45	10,5	299
072010646	7201BP 46	46	11	306
072010647	7201BP 47	47	12	313
072010648	7201BP 48	48	13	320

Scan the QR Code to access the web tab

Specs, media and documentation in one click.

