

Product Datasheet

Item No.: 62323

PRODUCT NAME

DuroConn single-socket extension lead 25 m H07RN-F 3G2.5 black IP54



Reference image



- for professional use – construction, industry, agriculture
- heavy-duty H07RN-F rubber cable
- resistant to oil, UV and ozone
- PowerLight voltage indicator
- fast and secure connection (quick-connect system)
- double safety contact
- self-closing socket flap
- high mechanical resistance
- operating temperature range: -30°C to +60°C (cable) / up to +80°C (connectors)
- IP54 protection – resistant to dust and water splashes
- colour: black-blue

Technical data

EAN	4011160623233
Weight [kg]	5.83
Dimensions	24x24x11 cm
Main color	black
Series	DuroConn
Category	Extensions
Subcategory	For use on construction sites
Cable type	H07RN-F
Cross section [mm²]	3G2,5
Cable color	black
Cable length [m]	25
Rated voltage [V]	230
Rated current [A]	16
Maximum power	3500 W
IP protection	IP54
Input	SCHUKOultra Pro plug red/black 230 V, 16 A, 2P+E, IP54
Output	1x SCHUKOultra Pro red-black socket 230 V, 16 A, 2P+E, IP54
Total number of sockets	1
Number of Type F sockets (230 V)	1
Number of cores	3

Your partner for professional lighting and electrical products.