

Technical Datasheet

tasker® K114 – 2x0,25 mm²

Low Capacity Balanced Microphone Cable



CATEGORY APPLICATIONS

Balanced Microphone Cable (See Audio Catalogue)
Pre-Made Audio Cables and Microphones.

- A:** Soft PVC Sheath Available in different colors.
Outer cable Diam. Ø 5,80 (±0,20) mm.
- B:** Shielding O.F.C. red copper Spiral covering 70%.
- C:** The cores are stranded in a pair with textile waste filler between conductors.
- D:** PVC core Insulations, colored one red and one white.
Diam. Ø 1,40 (±0,20) mm.
- E:** O.F.C. red copper, formation 8x0,20 mm.
Nom. Cross section 2x0,25 mm².

MARKING

tasker® K114 - 2x0.25 mm² - O.F.C. - Low Capacitance Microphone Cable - Made in Italy

CUSTOM PRODUCTION

This product may be custom produced also in **L.S.Z.H.** polymer, **PE**, **PUR**, or Metallic Armored.

Cable Properties

Conductor Resistance	75 Ω/Km
Capacity Core/Core	55 pF/m
Capacity Core/Shield	90 pF/m
Max Rated Voltage	49 V
Operative Temperature	-15/+70°C

USE	X	Indoor	Interno Edificio	INSTALLATION	X	Fixed	Fissa	INFORMATION	X	RoHS2 Compliant
Impiego		Outdoor Limited	Esterno Limitato	Posa	X	Restricted Mobile	Mobile Limitata	Informazioni	X	Ver. A / 16.05.16
		Outdoor	Esterno			Mobile	Mobile			
		Outdoor Direct Burial	Esterno Interrato			Mobile in Drag Chain	Mobile in Catena			