


1650
**Suwmiarka noniuszowa uniwersalna - Dokładność odczytu 0,05 mm -
 Dokładność odczytu 1/128"**
UNI EN ISO 13385-1DIN

	art.	A max mm	L mm	B mm	G mm	HxS mm	g
016500001	1650 150	150	235	40	0,05-1/128	16x3	170
016500002	1650 200	200	290	49	0,05-1/128		230

