


Antenna Cable N plug > SMA plug RG-58 C/U 10 m

Description

This antenna cable enables the connection between radio frequency technology components.



Item no. 89466

EAN: 4043619894666

Country of origin: China

Package: Zip poly bag

Technical details

- Connectors:
 - 1 x N plug >
 - 1 x SMA plug
- Impedance: 50 Ohm
- Cable: coaxial
- Cable type: RG-58 C/U
- Cable attenuation: 0.73 dB @ 1.0 GHz per meter
- Cable diameter: ca. 4.95 mm
- Smallest bending radius: 20 mm
- Cable colour: black
- Length incl. connectors: ca. 10 m

System requirements

- Device with one free N or SMA port

Package content

- Antenna cable

Images



Interface

Connector 1:	1 x N male
Connector 2:	1 x SMA plug

Technical characteristics

Impedance:	50 Ω
------------	-------------

Physical characteristics

Cable category:	coaxial
Cable type:	RG-58 C/U
Cable attenuation:	0.16 dB @ 100 MHz 0.73 dB @ 1.0 GHz per meter
Cable colour:	black
Cable length incl. connectors:	10 m
Smallest bending radius:	20 mm
Cable diameter:	4.95 mm

Manufacturer information

Street	Beeskowdamm 13/15
Postal code	14167
City	Berlin
Country	Deutschland
E-Mail	info@delock.de
Website	www.delock.de

