



BETA 7357G
0-Gravity ankle shoe,
ultralightweight, made of
water-repellent microfibre



Certifications and Standards

CE S3L FO SR HRO EN ISO 20345:2022

Features

The 7357G, featuring a water-repellent microfibre upper and soft collar, offers a combination of comfort, style and safety.

LIGHTNESS

The 0-Gravity shoe weighs approximately 100g less than the average work shoe.
The approximate weight is 480g (measured on size 42)

WATER PROTECTION

Made of water-repellent microfibre, the 0-Gravity 7356G offers a perfect balance of lightness, breathability and water resistance, representing a versatile and safe solution for those who never stop, even on the most demanding days

COMFORT AND DURABILITY

The durable nitrile rubber outsole provides strength and stability, while the EVA outsole offers lightweight cushioning.
Ideal for those looking for a reliable and comfortable shoe.



EVA FOAM UNDERFOOT COVER

The EVA underfoot cover, with a shock-absorbing heel pad, offers the perfect balance of support and comfort.



SOFT COLLAR

The collar, made of soft materials, offers effective protection while providing flexibility and comfort during use.



DESIGN AND STYLE

Safety does not go unnoticed, thanks to the upper details and innovative design.



Certifications and Standards

CE S3L FO SR HRO EN ISO 20345:2022



Specifications

LACING: traditional
 WEIGHT (INDICATIVE SIZE 42): 480 g
 TYPE: high

Lightness

REMARKABLY LIGHTWEIGHT - approximate weight for size 42: 480 grams

Comfort

EVA (Ethylene-Vinyl Acetate) FOAM underfoot cover with cushioning heel pad



Safety

Toe cap: polymer material, 200 joules
 Penetration-proof insole: composite fibre, ceramic treatment

Protections

Tip: • Microfibre upper, water-repellent, with TPU (Thermoplastic Polyurethane) inserts
 • Heel stability support
 • Stretch slip-on collar
 Durability: Sole:
 • EVA (Ethylene-Vinyl Acetate) mid-sole
 • Durable nitrile rubber tread

Coded items

	Art.	EU	UK	 mm
073570038	7357G 38	38	5	254
073570039	7357G 39	39	6	261
073570040	7357G 40	40	6,5	268
073570041	7357G 41	41	7	274
073570042	7357G 42	42	8	281
073570043	7357G 43	43	9	288
073570044	7357G 44	44	10	294
073570045	7357G 45	45	10,5	301
073570046	7357G 46	46	11	308
073570047	7357G 47	47	12	314
073570048	7357G 48	48	13	321

Scan the QR Code to access the web tab

Specs, media and documentation in one click.

