

Bellows suction cups (round)

FSGA 78 NK-45 G1/4-IG

Część nr.: 10.01.06.00421

<https://www.schmalz.com/10.01.06.00421>

Strona główna > Technologia podciśnienia w automatyce > Komponenty podciśnieniowe > Przyssawki podciśnieniowe > Przyssawki mieszkowe (okrągłe) > Przyssawki mieszkowe FSGA (1,5 fałdy) > FSGA 78 NK-45 G1/4-IG

Przyssawka mieszkowa (okrągła)



Size: 78

Suction cup material: Natural Rubber NK

Material hardness [Shore A]: 45 Shore A


Nipple material: Aluminum

Connection: G1/4"-F

Number of folds: 1,5

Vacuum connection: G1/4"-F

Dane projektowe



Atrybut	Wartość
d2	54 mm
Dmax(S)	84,50 mm
dn	8,20 mm
Ds	74 mm
G1	G1/4"-F
H	62 mm
LG1	12 mm
SW1	21 mm
Z (Stroke)	16 mm

Note: Acceptable dimensional tolerances for elastomer parts concerning to DIN ISO 3302-1 M3

Dane techniczne

Atrybut	Wartość
Suction cup material	Natural Rubber NK
Material hardness [Shore A]	45 Shore A
Size	78
Number of folds	1,50
Connection	G1/4-IG
Curve radius (min) (convex)	100 mm
Volume	75,58 cm ³

Kontakt z firmą Schmalz

Schmalz Sp.z.o.o. | ul. Fabianowska 131/A1, 62-052 Komorniki, Poland | +48 61 628 67 70 | schmalz@schmalz.pl

Bellows suction cups (round)

FSGA 78 NK-45 G1/4-IG

Część nr.:10.01.06.00421

<https://www.schmalz.com/10.01.06.00421>

Suction force (-600mbar)	137,40 N
Pull-off force	218 N
Hose diameter (empf.) d	6 mm
Weight	71 g
Product family	FSGA

Note: Suction force: The specified suction forces are theoretical values at a vacuum of -0.6 bar and with a dry, smooth and flat workpiece surface - they do not include a safety factor Pull-off force: The pull-off force of the versions made of natural rubber is reduced by about 40% Hose diameter: The recommended hose diameter refers to a hose length of approx. 2 m

Części zamienne



FGA 78 NK-45 N019

Część nr.:10.01.06.00429

Size: 78

Suction cup material: Natural Rubber NK

Material hardness [Shore A]: 45 Shore A

Number of folds: 1,5