USB 10 Gbps Hub with 3 x USB Type-A and 1 x USB Type-C™ female with Switch

Description

The USB hub by Delock can be connected via USB Type-C™ interface to a PC or laptop. It has **three USB Type-A connectors as well as one USB Type-C™ connector**. Different USB devices such as USB flash memory, card reader, external enclosure etc. can be connected.



Individual switch

Each port can be **turned on or off** individually by using the switches.

Item no. 64384

EAN: 4043619643844

Country of origin: China

Package: Retail Box

Technical details

- Connectors:
  1 x USB 10 Gbps USB Type-C™ male
  1 x USB 10 Gbps USB Type-C™ female
  3 x USB 10 Gbps Type-A female
- Data transfer rate up to 10 Gbps
- 4 x LED indicator
- 4 x switch
- Robust metal housing
- Electrical power (depends on host, distribution of total power to individual ports):
  total: max. 15 watt (5 V / 3 A)
  USB Type-C™: max. 15 watt (5 V / 3 A)
  USB Type-A: max. 4.5 watt (5 V / 0.9 A)
- Bootable
- Colour: grey
- Plug & Play
- Cable length: ca. 60 cm
- Cable with textile shielding
- Dimensions (LxWxH): ca. 102 x 30 x 12 mm

System requirements

All names and symbols mentioned here are property of the respective producer. Printing errors, changes and errors excepted. **© 2026 by Delock. All rights reserved.**

- Chrome OS
- Linux Kernel 6.2 or above
- Mac OS 14.2.1 or above
- Windows 10/10-64/11
- iPad Air (4th Generation) or above
- iPad Pro (3rd Generation) or above
- iPhone 15 Pro or above
- Device with a free USB Type-C™ port or with a free Thunderbolt™ 3, Thunderbolt™ 4 or Thunderbolt™ 5 port

Package content

- Hub USB 10 Gbps
- User manual

Images







All names and symbols mentioned here are property of the respective producer. Printing errors, changes and errors excepted. **© 2026 by Delock. All rights reserved.**

General

Function:	Plug & Play bootable
Supported operating system:	Chrome OS Windows 10 32-Bit Windows 10 64-Bit iPad Pro (3rd Generation) or above iPad Air (4th Generation) or above Windows 11 Linux Kernel 6.2 or above iPhone 15 Pro or above Mac OS 14.2.1 or above
LED indicator:	4 x

Interface

Connector:	1 x USB 10 Gbps USB Type-C™ male 1 x USB 10 Gbps USB Type-C™ female 3 x USB 10 Gbps Type-A female

Technical characteristics

Electrical power per port:	USB Type-C™: max. 15 watt (5 V / 3 A) USB Type-A: max. 4.5 watt (5 V / 0.9 A) max. 15 watt (5 V / 3 A)
Data transfer rate:	10 Gbps

Physical characteristics

Housing material:	metal

All names and symbols mentioned here are property of the respective producer. Printing errors, changes and errors excepted. **© 2026 by Delock. All rights reserved.**

Cable length:	60 cm
Length:	102 mm
Width:	30 mm
Height:	12 mm
Colour:	grey

Manufacturer information

Street	Beeskowdamm 13/15
Postal code	14167
City	Berlin
Country	Deutschland
E-Mail	info@delock.de
Website	www.delock.de

All names and symbols mentioned here are property of the respective producer. Printing errors, changes and errors excepted. **© 2026 by Delock. All rights reserved.**