



BETA 7340VA RENEGADE mesh fabric shoe, highly breathable, with ATOP lacing



Certifications and Standards

CE S1PS FO SR HRO EN ISO 20345:2022

Features

The 7340VA safety footwear guarantees style, comfort and breathability, with the advantage of the ATOP lacing system.

SAFETY WITH STYLE

The shoe that offers protection without sacrificing looks.

Thanks to the "urban" style, inspired by sports shoes, it is also perfect to wear after work.

EXTREME COMFORT

Renegade combines advanced cushioning and superior support to provide exceptional comfort throughout the working day.

Thanks to its innovative design and high performance, it ensures a smooth and comfortable walk.

WIDE FOOTBED

The wide fit further enhances the comfort of the shoe, preventing possible constriction of the foot at any time of day.

BREATHABLE AND RESISTANT

The mesh upper, thanks to its open construction, offers exceptional lightness and optimal breathability. Its remarkable durability makes it perfect for ensuring a long life without compromising on quality.



INNOVATIVE DESIGN

The 7340VA shoe combines sporty design and modern style, highlighting an innovative outsole that ensures safety and comfort with every step.



ATOP QUICK LACING

ATOP lacing offers precise and quick adjustment for greater stability.



MAXIMUM RESISTANCE

The rubber outsole makes the shoe extremely durable and heat-resistant up to 300°C.



Certifications and Standards

CE S1PS FO SR HRO EN ISO 20345:2022



Specifications

LACING:	traditional
WEIGHT (INDICATIVE SIZE 42):	495 g
TYPE:	low

Lightness

- Highly breathable mesh fabric with TPU (thermoplastic polyurethane) inserts
- Heel stability support
- ATOP lacing

Comfort

- EVA (ethylene vinyl acetate) midsole
- Durable nitrile rubber tread

Safety



EVA FOAM underfoot cover

Protections

Tip: Polymer material, 200 joules

Durability: Composite fibre, ceramic treatment

Coded items

	Art.	EU	UK	 mm
073400537	7340VA 37	37	4,5	248
073400538	7340VA 38	38	5	254
073400539	7340VA 39	39	6	261
073400540	7340VA 40	40	6,5	268
073400541	7340VA 41	41	7	274
073400542	7340VA 42	42	8	281
073400543	7340VA 43	43	9	288
073400544	7340VA 44	44	10	294
073400545	7340VA 45	45	10,5	301
073400546	7340VA 46	46	11	308
073400547	7340VA 47	47	12	314
073400548	7340VA 48	48	13	321

Scan the QR Code to access the web tab

Specs, media and documentation in one click.

