

Antenna Cable FME Jack > SMA Plug RG-58 7.5 m

Description

The coaxial antenna cable by Delock allows the connection of devices, in addition it is suitable for connection to the antenna mounting foot [Delock 12484](#).



Item no. 12450

EAN: 4043619124503

Country of origin: Taiwan,
Republic of China

Package: Poly bag

Technical details

- Connectors:
 - 1 x FME jack
 - 1 x SMA plug
- Impedance: 50 Ohm
- Cable category: coaxial
- Cable type: RG-58
- Cable attenuation: 0.4 dB @ 500 MHz per meter
- Cable diameter: ca. 4.95 mm
- Cable colour: black
- Minimum bending radius: 2 cm
- Cable length incl. connectors: ca. 7.5 m


System requirements

- One free FME plug
- One free SMA jack

Package content

- Antenna cable

Images



Interface

Connector 1:	1 x FME jack
Connector 2:	1 x SMA plug

Technical characteristics

Impedance:	50 Ω
------------	-------------

Physical characteristics

Cable category:	coaxial
Cable type:	RG-58
Cable attenuation:	0.4 dB @ 500 MHz per meter
Cable colour:	black
Cable length incl. connectors:	7.5 m
Smallest bending radius:	2 cm
Cable diameter:	4.95 mm

Manufacturer information

Street	Beeskowdamm 13/15
Postal code	14167
City	Berlin
Country	Deutschland
E-Mail	info@delock.de
Website	www.delock.de

