



**Flexible strain relief for cables  
model : F5x2.5/25**

### Dimension

|                                     |                 |
|-------------------------------------|-----------------|
| Cable cross section (A)             | 5.0 x 2.5 mm    |
| Total length (F)                    | 25mm            |
| Working length (E)                  | 19mm            |
| Width (B)                           | 8.9mm           |
| Width (D)                           | 8.5mm           |
| Mounting hole (C)                   | Max 6.7 x 3.3mm |
| Maximum mounting wall thickness (G) | 3.4mm           |

### Other

Material

- Hydrogenated styrene butadiene block copolymer (SEBS)
- Hydrogenated styrene isoprene butadiene block copolymer (SEEPS)
- Ethylene Propylene Diene Monomer (EPDM)
- Styrene butadiene styrene block copolymer (SBS)

