

Producer	Qoltec
Scanner type	Image
Scan Type	Single line
Input voltage	5 V
Scanning speed	300 scans / sec.
Barcode Types	1D, 2D
Scanning depth	EAN-13: 50-200 mm, Code 39: 40-90 mm, QR: 20.5-240 mm, Data marix: 50-90 mm, PDF 417: 30-130 mm
Scan mode	Manual, continous sensing, auto-sensing
Scanning Angel	360 roll slope of 65 deviation of 65
Operating current	370 mW (working), 160 mW (stanby), 710mW (maximum)
Processor	32 bit
Print contrast	25 %
Interface	WT 2.4GHz, USB
Source of light	Red LED (aiming) + White LED (lighting)
Shock resistance	1.5 m
Resolution	4 mils
Working time	8 h
Range	70 - 100 m (open area)
Scanning distance	10 - 600 mm
Supported operating systems	Windows XP/7/8/10 Android Linux MAC
Signalization	By sound
Cable length	1.8 m
Type	Wireless / Wired
Usage	Shops Warehouses Offices Libraries Logistic points
Additional information	Lithium battery: 3.7V, 2000, maH Supported languages: English, German, French, Spanish, Italian, Japanese
Other parameters	
Material	ABS + PVC + PC
EAN code	5901878508689