
mm [inch]






**ST1011 UB04 SX**

| | |
|---|---|
| Minimum centers: | 2.54 [.100] |
| Full travel: | 4.20 [.165] |
| Working travel: | 2.80 [.110] |
| Current rating: | 3 A |
| Probe resistance: | < 100 mΩ |
| Plunger material: | BeCu / Gold plated |
| Barrel material: | Nickel-Silver / Gold plated |
| Spring material: | Steel / Gold Plated |

Spring force at working stroke: 1.0 N [3.6 oz]

© COPYRIGHT 2019
EQUIP-TEST KFT.
ALL RIGHTS RESERVED
This drawing, model, intellectual product belongs to Equip-Test Kft. Forwarding it to 3rd. party, copying it or using for any other purpose without the written approval of Equip-Test Kft., could entail to legal and criminal procedure!

| | Name | Date |
|---|---|---|
| Designed | Cs.V. | 04.05.2019 |
| Drawed | | |
| Checked | | |
| Note | | |

Catalog Item: **ST1011 UB04 SX**

Drawing No.:

A4 | SHEET 1 OF 1

EQUIP TEST
TEST – SUPPORT – INNOVATE