

Power cord (C13 to C14), 0.75 mm², 10 A, 1.8 m

PC-189-075-1.8M



Features

- Power (extension) cord with C13 input and C14 output
- Molded plugs with integrated strain relief

Specifications

Rating: 250 V~, 10 A (2500 W)
 Wire diameter: 3 x 0.75 mm²
 Connector 1: C13
 Connector 2: C14
 Length: 1.8 m

Packaging

Q'ty in crtn, pcs	60
Crtn volume, CUM	0.04
Crtn weight, kgs	11
Individual package size LxWxH:	175x120x40 mm
Carton size LxWxH:	400x300x330 mm
Country of origin	CN
Barcode	8716309023757
Customs code	8544429090

Certificates

