



HAWK 2

LASER MOUSE

PRODUCT FEATURES:

- A precise laser sensor provides smooth and reliable operation on all surfaces, including glass.
- The ergonomic shape fits your hand, reducing fatigue and increasing comfort even during long hours of work.
- Durable buttons, designed for millions of clicks, guarantee long-term reliability and consistent performance.
- Four DPI levels allow you to quickly change the cursor sensitivity and easily adjust it to your individual needs.
- Teflon glides ensure smooth mouse movement on any surface, increasing precision and reducing wrist fatigue.
- The long USB cable offers freedom to arrange your workspace and a stable connection without interference.



PRODUCT SPECIFICATION:

Communication	Wired
Interface	USB
Sensor	Laser
Maximum resolution	up to 2 400 DPI
DPI levels	800-1200-1600-2400
Number of buttons	4
Cable length	180 cm
Supported Operating Systems	Android, Linux, Windows 8, Windows 10, Windows 7
Dimensions	119 x 64 x 40 mm

